

項目	ABS樹脂板厚2.0mm
単位	mm
公差	±0.1mm
寸法	10mm×20mm×50mm×100mm
色	黒色
表面	平滑
特性	高強度

ABS樹脂板厚2.0mmの寸法公差は、ISO13485規格に準拠しています。ABS樹脂板の寸法公差は、ISO13485規格に準拠しています。

単位

- ABS樹脂板厚2.0mm
- 単位mm
- 公差±0.1mm
- ISO13485規格に準拠
- ISO9001規格に準拠

ABS樹脂板厚2.0mmの寸法公差は、ISO13485規格に準拠しています。ABS樹脂板の寸法公差は、ISO13485規格に準拠しています。




品質保証

品質保証書を添付しております。

- **ISO 13485** 品質マネジメントシステム認証取得済み
- **ISO 9001** 品質マネジメントシステム認証取得済み
- **FDA** 米国FDAから承認を受けています。
- **CE MDR** 欧州CE MDR認証取得済み。

お問い合わせ



About Us

10+ Years Experienced Professional Manufacturer
of Customized Cables.



2000 M²
Factory space with 10 years
of production experience



100+
Employees



OEM/ODM
Support cable customized



TOP 500
Bands approved
manufacturer



Certificate

We followed international ISO management Standard to make our custom cables,
medical cables and chargers with good quality and best price.



ISO13485

FCC

CE

RoHS



UKCA

EPR

EPR

ISO9001

□ □ □ □

Q1

Heymed

Q2

PayPal T/T L/C

3

□□□□□□□□□□□□□□QC□□□□□□□□□□□□□□□□□□ROHS□SGS□CE FCC□ISO9001□2008□□□ ETC

4

100 OEM/ODM

5

□□□□□□□□2-4□□□□□□□□12□□□□□□□□□□DHL□FedEx□UPS□TNT□EMS□□□□□□

0060000000000000

□□□□□□□□□□Dongguan□□□□□□□□□□□□□□□□ A Building A□8□□□□□□□□□□Shebei□

□Kangyang 1st Street□Shebei□