

產品名稱	Customized Hirose Plug ~ 4 芯 2.0mm 间距 连接器 Dongguan 德昌五金
規格	4 芯, 2.0mm 间距
長度	10cm, 20cm, 50cm, 100cm 等
材料	銅, 鍍金, 鍍銀 等
包裝	1000 個/包
備註	可定制

本產品符合 ISO13485 標準，品質可靠。適用於各種電子設備連接。4 芯 2.0mm 间距，連接牢固，使用壽命長。

產品特點：
1. 间距：2.0mm
2. 芯數：4 芯
3. 長度：10cm, 20cm, 50cm, 100cm 等
4. 材料：銅, 鍍金, 鍍銀 等
5. 包裝：1000 個/包
6. 備註：可定制

OEM/ODM 服務：我們提供專業的 OEM/ODM 服務，可根據客戶需求定制各種規格、顏色、長度、材料等。歡迎垂詢。

Dongguan 德昌五金 專業生產各種規格、顏色、長度、材料等。歡迎垂詢。





□□ □ □□ □□ :

□ □□□□ □□ □□□□ □□ □□ □ □□ □□□□ □□ □□□ □□□ □□□□□.

- **ISO 13485** : □□□ □□ □□ □□ □□ □□□□ □□ □□ □□□□□.
- **ISO 9001** : □□□ □□ □□ □□□□□ □□□□□□□□□□.
- **FDA** □□ : □ □□□ □□ □□□ □□□ □□□□ □□ □□ □□□ □□□□□.
- **CE MDR** □□ : □□ □□□ □□□□ □□□ □□□ □□ EU □□ □□ □□ (MDR)□ □□□□□.

□□ □□. □□



About Us

10+ Years Experienced Professional Manufacturer of Customized Cables.



2000 M²
Factory space with 10years
of production experience



100+
Employees



OEM/ODM
Support cable customized



TOP 500
Bands approved
manufacturer



Certificate

We followed international ISO management Standard to make our custom cables, medical cables and chargers with good quality and best price.



ISO13485

FCC

CE

ROHS



UKCA

EPR

EPR

ISO9001

FAQ

Q1 : 我 可以 拿 到 樣 品 嗎 ？

A : 可以, Heymed 可以 提供 樣 品 給 您 參考. 但是 樣 品 不 能 大批 拿 取. 樣 品 拿 取 請 到 廠 面 洽 談.

Q2 : 我 可以 拿 到 樣 品 嗎 ？

A : PayPal, T/T, 匯 豐, Western Union 均 L/C.

Q3 : 我 可以 拿 到 樣 品 嗎 ？

： 可以 拿 到 樣 品. 我 們 有 樣 品 庫 存 QC 樣 品 庫 存 樣 品 均 有 樣 品 庫 存. 樣 品 ROH, SGS, CE FCC, ISO9001 : 2008 樣 品 庫 存. 均

Q4 : 我 ？ ！ 我 們 有 樣 品 嗎 ？

A : 可以. 樣 品 均 有 100 均 有 樣 品 庫 存. OEM/ODM 樣 品 庫 存. 樣 品 均 有 樣 品 庫 存.

Q5 : 我 有 樣 品 嗎 ？ 我 有 樣 品 嗎 ？

A : 我 有 樣 品 均 2-4 樣 品 均 有 12 樣 品 均 有 樣 品 庫 存. 樣 品 DHL, FedEx, UPS, TNT, EMS 均 有 樣 品 庫 存.

Q6 : 我 有 樣 品 嗎 ？ 我 有 樣 品 嗎 ？

： 可以. 樣 品 Dongguan 樣 品 庫 存 樣 品 均 有 樣 品 庫 存. 樣 品 均 有 樣 品 庫 存. A, No. 8, Kangyang 1st Street, Shebyi Village, Huangjiang Town, Dongguan City, Guangdong Province, 均