

RS232 規格

規格	RS232 規格 15ピン DB15 ケーブル - Molex ケーブル
メーカー	Molex DB15pin ケーブル
ケーブル 長さ	30cm ケーブル ケーブル
ケーブル 色	ケーブル ケーブル
用途	プリンター, 外部, ケーブル, POS ケーブル, ケーブル, ケーブル
単位	ケーブル ケーブル
MOQ	100PCS

ケーブル ケーブル ケーブル Molex ケーブル ケーブル D-sub ケーブル DB15pin ケーブル ケーブル, ケーブル ケーブル ケーブル D-SUB ケーブル ケーブル. [ケーブル ケーブル ケーブル](#), ケーブル [DB25 ケーブル-ケーブル ケーブル ケーブル](#) ケーブル, ケーブル 25 ケーブル ケーブル ケーブル ケーブル. ケーブル ケーブル D-sub ケーブル ケーブル. [. ケーブル](#)

D-sub ケーブル ケーブル ケーブル ケーブル ケーブル ケーブル ケーブル ケーブル.

[ケーブル ケーブル](#):





□□□□.□□



About Us

10+ Years Experienced Professional Manufacturer
of Customized Cables.



2000 M²
Factory space with 10 years
of production experience



100+
Employees



OEM/ODM
Support cable customized



TOP 500
Bands approved
manufacturer



Certificate

We followed international ISO management Standard to make our custom cables,
medical cables and chargers with good quality and best price.



□□□□□□

Q1: □ □□□□ □□ □□ □□□ □ □□□□?

A: □□□□□. Heymed□ □□□ □□ □□ □□ □□□□□, □□□ □□□ □□ □□□ □□□□ □□□. □□□ □□□□ □□ □□□ □□□ □□□□□□□□□□□.

Q2: □□ □□ □□□ □□□□□?

A: □□□, T/T, □□ □□, □□□□□□ □ L/C

Q3: □□□ □□ □□□ □□□□ □□ □□□□?

A: □□□ □□□□□□. □□ □□ □□ □□□□ □□ QC □□□ □□□□ □□□ □□ □□□ □□□□□□□□□□. □□ □□□ **Rohs, SGS, CE FCC, ISO9001:2008** □□□ □□□□□□□□. □

Q4: □□? □! □□□ □□□ □□□□□ □□□□ □□□ □□□ □□□ □□□□□ □□□□□?

A: □□□□□, □□□ 100□ □□ □□□ □□ □□□□□□. □□□ **OEM/ODM** □□□□ □□□□□□. □□□ □□□ □□ □□ □□ □□□□□ □□□□□□□.

Q5: □□ □□ □ □□? □ □□□ □□ □□ □□□□ □□□□□?

A: □□ □□□ □ 2-4□□□ □□ □ 12□□ □□□ □□□ □ □□□□□. □□□ **DHL, Fedex, UPS, TNT, EMS**□ □□□□ □□□□□□.

Q6: □□□ □□□ □□□□? □□□ □□□ □□□ □ □□□□?

A: □□□□□□. □□□□ □□ □□□□ □□ □□□ □□□□ □□ □□□□□. □□ □□□ 3rd□ □□□□□. □□ □□□□□□ □□□□□□ □□1□□ 8□
A□ 1□