

產品規格

規格	DC55*25mm 板對板 HDMI 母座 25pin Y 型 板對板 DB9 母座
規格	DB9 母座-HDMI 母座 DC5525 母座
規格	30cm 板對板
規格	板對板 板對板
規格	板對板, 板對板, 板對板, POS 板對板, 板對板, 板對板
規格	板對板 板對板
MOQ	100PCS

DC5525 板對板 板對板 HDMI 母座 25pin RS232 母座 25pin Y 型 D-sub DB9pin 母座, 板對板 板對板 板對板 DB9pin 母座HDMI 母座DC55*25mm 板對板 板對板. 板對板, 板對板 ODM OEM 板對板 板對板 板對板 板對板, ~板對板 [RJ45 板對板 板對板 板對板 板對板](#).


板對板, 板對板 板對板 板對板 D-sub 板對板, [DB25 母座-RS232 母座 25pin](#) , RS232 25Pins 板對板, 板對板 板對板 板對板 板對板. 板對板 DB25 母座 板對板 板對板 板對板 板對板 板對板 板對板 板對板. 板對板 板對板 D-sub 板對板 板對板. [.](#)

產品圖:





□□□□.□□



About Us

10+ Years Experienced Professional Manufacturer
of Customized Cables.



2000 M²
Factory space with 10 years
of production experience



100+
Employees



OEM/ODM
Support cable customized



TOP 500
Bands approved
manufacturer



Certificate

We followed international ISO management Standard to make our custom cables,
medical cables and chargers with good quality and best price.



□□□□□□

Q1: □ □□□□ □□ □□ □□□ □ □□□□?

A: □□□□□. Heymed□ □□□ □□ □□ □□ □□□□□, □□□ □□□ □□ □□□ □□□□ □□□. □□□ □□□□ □□ □□□ □□□ □□□□□□□□□□□.

Q2: □□ □□ □□□ □□□□□?

A: □□□, T/T, □□ □□, □□□□□□ □ L/C

Q3: □□□ □□□ □□ □□□ □□□□ □□□ □□ □□□□?

A: □□□ □□□□□□. □□□□ □□ □□ □□□□ □□ QC □□□ □□□□ □□□□□ □□ □□□ □□ □□□□ □□□□□□□. □□ □□□ **Rohs, SGS, CE** **FCC, ISO9001:2008** □□□ □□□□□□□. □

Q4: □□? □! □□□ □□□ □□□□□ □□□□ □□□ □□ □□□ □□□ □□□□□ □□□□□?

A: □□□□□, □□□ 100□ □□ □□□ □□ □□□□□. □□□ **OEM/ODM** □□□□ □□□□□. □□□ □□□ □□ □□ □□ □□□□□ □□□□□□□.

Q5: □□ □□ □ □□? □ □□□ □□ □□ □□□□ □□□□□?

A: □□ □□□ □ 2-4□□□ □□ □ 12□□ □□□ □□□ □ □□□□□. □□□ **DHL, Fedex, UPS, TNT, EMS**□ □□□□ □□□□□□.

Q6: □□□ □□□ □□□□? □□□ □□□ □□□ □ □□□□?

A: □□□□□. □□□□ □□ □□□□ □□ □□□ □□□□ □□ □□□□□. □□ □□□ 3rd□ □□□□□. □□ □□□□□□ □□□□□ □□1□□ 8□
A□ 1□