

□□ □□□□

□□□	DB9 9P □ □□□ - RJ12 6P6C LAN □□□□ □□ □□ □□□
□□□	RJ12 □ □□□□ DB9pin □
□□□ □□	30cm □□ □□□
□□□ □□	□□ □□ □□□
□□□□	□□□, □□□, □□□, POS □□, □□□, □□
□□	□□ □□□ □□
MOQ	100PCS

□ DB9 - RJ12 6P6C RS232 □□ □□ □□□□ RS-232 □□(COM □□) □□□□□□ □□ □□□ □□□□ □□□□ sevo □□□ □ □□□ □□□ □□□ □□□ □□□□ ODM OEM □□□ □ □□□ □□□□ □□□□□. ♪

□ □□□, □□□ □□ RJ45 8P8C □□ □□ □□□, □□□, □□□□ □□ RS232 9Pins ni-plated □□□ □□ □□ □□□□ DB9 □□ □□ □□ □□□□ □□ □□ D-sub □□□□, □□□ □□□□. □□□ □□□ □□□ □□□ D-sub □□□□ □□□□. ♪

□□ □□:





00 00. 00



About Us

10+ Years Experienced Professional Manufacturer of Customized Cables.



2000 M²
Factory space with 10years of production experience



100+
Employees



OEM/ODM
Support cable customized



TOP 500
Bands approved manufacturer



Certificate

We followed international ISO management Standard to make our custom cables, medical cables and chargers with good quality and best price.



ISO 13485

FCC

CE

ROHS



UKCA

EPR

EPR

ISO 9001

□□□□ □□

Q1: □ □□□□ □□ □□ □□□ □□□□□?

A: □□□□□. Heymed□ □□□ □□ □□ □□ □□□ □□□□, □□□ □□□ □□ □□□ □□□□ □□□. □□□ □□□□ □□ □□□ □□□ □□□□□□□.

Q2: □□ □□ □□□ □□□□□?

A: □□□, T/T, □□ □□, □□□ □□□ □ L/C

Q3: □□□ □□ □□□ □□□□ □□□ □□ □□□□?

A: □□□ □□□□□□. □□□□ □□ □□ □□□□ □□ QC □□□ □□□□ □□□ □□ □□□ □□ □□□□ □□□□□□. □□ □□□ Rohs, SGS, CE FCC, ISO9001:2008 □□□ □□□□□□□. □

Q4: □□? □! □□□ □□□ □□□□□ □□□□ □□□□ □ □□ □□□□ □□□ □□□ □□□ □ □□□□?

A: □□□□□, □□□ 100□ □□ □□□ □□ □□□□□. □□□ OEM/ODM □□□□ □□□□□□□. □□□ □□□ □□ □□ □□ □□□□□ □□□□□□□.

Q5: □□ □□ □ □□? □ □□□ □□ □□ □□□□ □□□□□?

A: □□ □□□ □ 2-4□□□□ □□ □ 12□□ □□□ □□□ □ □□□□. □□□ DHL, Fedex, UPS, TNT, EMS□ □□□□ □□□□□□□.

Q6: □□□ □□□ □□□□? □□□ □□□ □□□ □ □□□□?

A: □□□□□□. □□□ □□ □□ □□□□ □□ □□□ □□□□ □□ □□ □□□□. □□ □□□ 3rd□ □□□□□. □□ □□□ □□□ □□□ □□□□ □□1□□ 8□ A□ 1□