


## Product parameters

|                    |                                                                           |
|--------------------|---------------------------------------------------------------------------|
| Product Name       | 12V Powered USB Coiled Cable with RJ50 Male Connector for Printer Scanner |
| Connector          | 12V powered USB cable and RJ50 10P10C connector                           |
| Cable Length       | 30cm or customized                                                        |
| Cable Color        | Grey or customized                                                        |
| Applied equipments | Extension, POS system, Printer, Bar Code Scanner etc                      |
| Function           | Connect POS scanners and printers to a PC for power and connectivity      |
| MOQ                | 100PCS                                                                    |

This high-end [12V powered USB extension cable](#) with RJ50 male connector provides the ability to supply power and communication signals using a single cable. The new innovative powered USB technology is extremely useful for the retail POS, industrial, security and for medical devices. It provides genuine, and convenient single cable plug-and-play connectivity and is supported by high quality design and construction needed to support the complex new devices. It provides superb grounding and protection for all components, as well as protection against the normal wear and tear that can result from repeated insertions and removals. It eliminates external power supply needs for USB peripheral devices such as receipt printers, signature capture devices and bar-code scanners.

### Product Photo:









## **Company Info. Overview**



## About Us

10+ Years Experienced Professional Manufacturer of Customized Cables.



2000 M<sup>2</sup>  
Factory space with 10years of production experience



100+  
Employees



OEM/ODM  
Support cable customized



TOP 500  
Bands approved manufacturer



## Certificate

We followed international ISO management Standard to make our custom cables, medical cables and chargers with good quality and best price.



ISO 13485

FCC

CE

ROHS



UKCA

EPR

EPR

ISO 9001

# FAQ

## **Q1: Can I start a sample order before I order more?**

A: Sure, Heymed provide free sample if we have stock, customized sample need to be charged setup cost. We appreciate you asking us for a sample to check our quality.

## **Q2: What payment methods do you accept?**

A: PayPal, T/T, Bank Transfer, Western Union and L/C

## **Q3: How is your factory doing regarding quality control?**

A: Quality is priority. QC department with professional quality assurance specialist attaches great importance to quality control from the very beginning to the very end. Our factory has obtained Rohs, SGS, CE FCC, ISO9001:2008 authentication. Etc

## **Q4: Factory? Yes! Can I customize the items I like, such as print our own logo or modify the design?**

A: Yes, we are a factory with more than 100 employees. We offer OEM/ODM service. Please contact us or our sales representative for details.

## **Q5: Delivery time and warranty? What shipping service will you use for my products?**

A: Our lead time is around 2-4 weeks and we can offer 12 months warranty from delivery. We use DHL, Fedex, UPS, TNT, EMS as the customer.

## **Q6: Where is your factory located? How can I visit there?**

A: Sure. We are more than happy to welcome you to Dongguan and show you around our workplace. Our factory is located in 3rd. Floor, Building A, No.8 Kangyang 1st Street, Shebei Village, Huangjiang Town, Dongguan City, Guangdong, China.