


Product parameters

Product Name	12V Powered USB to RJ50 LAN Ethernet Adapter Cable For Computer Printer
Connector	12V powered USB cable and RJ50 10P10C connector
Cable Length	30cm or customized
Cable Color	Black or customized
Applied equipments	Extension, POS system, Printer,Bar Code Scanner,Computer etc
Function	Connect POS scanners and printers to a PC for power and connectivity
MOQ	100PCS

This high-end [12V powered USB extension cable](#) with RJ50 male connector provides the ability to supply power and communication signals using a single cable. The new innovative powered USB technology is extremely useful for the retail POS, industrial, security and for medical devices. It provides genuine, and convenient single cable plug-and-play connectivity and is supported by high quality design and construction needed to support the complex new devices. It provides superb grounding and protection for all components, as well as protection against the normal wear and tear that can result from repeated insertions and removals.It eliminates external power supply needs for USB peripheral devices such as receipt printers, signature capture devices and bar-code scanners.

We also have other color 12V powered cord USB cable,such as [12V powered USB extension cable with RJ50 connector](#).

Product Photo:





Company Info. Overview



About Us

10+ Years Experienced Professional Manufacturer
of Customized Cables.



2000 M²
Factory space with 10 years
of production experience



100+
Employees



OEM/ODM
Support cable customized



TOP 500
Bands approved
manufacturer



Certificate

We followed international ISO management Standard to make our custom cables,
medical cables and chargers with good quality and best price.



ISO13485

FCC

CE

RoHS



UKCA

EPR

EPR

ISO9001

FAQ

Q1: Can I start a sample order before I order more?

A: Sure, Heymed provide free sample if we have stock, customized sample need to be charged setup cost. We appreciate you asking us for a sample to check our quality.

Q2: What payment methods do you accept?

A: PayPal, T/T, Bank Transfer, Western Union and L/C

Q3: How is your factory doing regarding quality control?

A: Quality is priority. QC department with professional quality assurance specialist attaches great importance to quality control from the very beginning to the very end. Our factory has obtained Rohs, SGS, CE FCC, ISO9001:2008 authentication. Etc

Q4: Factory? Yes! Can I customize the items I like, such as print our own logo or modify the design?

A: Yes, we are a factory with more than 100 employees. We offer OEM/ODM service. Please contact us or our sales representative for details.

Q5: Delivery time and warranty? What shipping service will you use for my products?

A: Our lead time is around 2-4 weeks and we can offer 12 months warranty from delivery. We use DHL, Fedex, UPS, TNT, EMS as the customer.

Q6: Where is your factory located? How can I visit there?

A: Sure. We are more than happy to welcome you to Dongguan and show you around our workplace. Our factory is located in 3rd. Floor, Building A, No.8 Kangyang 1st Street, Shebei Village, Huangjiang Town, Dongguan City, Guangdong, China.