

## Product parameters

Product Name	24V PoweredUSB Extension Cable with DC Male Connector
Connector	24V poweredUSB,DC55525&DC5525 male connector
Cable Length	30cm or customized
Cable Color	Black or customized
Applied equipments	Extension, POS system, Printer,Bar Code Scanner,Computer etc
Function	Connect POS scanners and printers to a PC for power and connectivity
MOQ	100PCS

This [24V powered USB cable](#) with DC power right angle male connector,have 55\*21mm&55\*25mm,allows the extension of a PoweredUSB connection and can be used to connect various devices. The cable is used both for data transmission and for power supply of the connected device,it can transmit data at a high-transfer speed.

It provides superb grounding and protection for all components, as well as protection against the normal wear and tear that can result from repeated insertions and removals.It eliminates external power supply needs for USB peripheral devices such as receipt printers, signature capture devices and bar-code scanners.

We also have other color 12V powered cord USB cable,such as [12V powered USB extension cable with RJ50 connector](#).

## Product Photo:









**Company Info. Overview**



## About Us

10+ Years Experienced Professional Manufacturer  
of Customized Cables.



2000 M<sup>2</sup>  
Factory space with 10 years  
of production experience



100+  
Employees



OEM/ODM  
Support cable customized



TOP 500  
Bands approved  
manufacturer



## Certificate

We followed international ISO management Standard to make our custom cables,  
medical cables and chargers with good quality and best price.



## FAQ

### **Q1: Can I start a sample order before I order more?**

A: Sure, Heymed provide free sample if we have stock, customized sample need to be charged setup cost. We appreciate you asking us for a sample to check our quality.

### **Q2: What payment methods do you accept?**

A: PayPal, T/T, Bank Transfer, Western Union and L/C

### **Q3: How is your factory doing regarding quality control?**

A: Quality is priority. QC department with professional quality assurance specialist attaches great importance to quality control from the very beginning to the very end. Our factory has obtained Rohs, SGS, CE FCC, ISO9001:2008 authentication. Etc

### **Q4: Factory? Yes! Can I customize the items I like, such as print our own logo or modify the design?**

A: Yes, we are a factory with more than 100 employees. We offer OEM/ODM service. Please contact us or our sales representative for details.

### **Q5: Delivery time and warranty? What shipping service will you use for my products?**

A: Our lead time is around 2-4 weeks and we can offer 12 months warranty from delivery. We use DHL, Fedex, UPS, TNT, EMS as the customer.

### **Q6: Where is your factory located? How can I visit there?**

A: Sure. We are more than happy to welcome you to Dongguan and show you around our workplace. Our factory is located in 3rd. Floor, Building A, No.8 Kangyang 1st Street, Shebei Village, Huangjiang Town, Dongguan City, Guangdong, China.