

## Product parameters

Product Name	Ear Clip Oximeter Sensors with 3.5mm Male Audio Jack for Ear Pulse Oximeters
Connector	3.5mm audio jack,SpO2 ear clip sensor
Cable Length	30cm or customized
Cable Color	Medical gray or customized
Function	TENS EMS Transmission,Pulse Oximeters
MOQ	100PCS

This ear clip sensor with 3.5mm audio jack and provides an alternative site for pulse oximetry. In some cases, access to a patient's hands and feet may not be available, or the hands may not be receiving sufficient blood flow,so we offers an ear clip pulse oximeter sensor.This setup works well for both continuous monitoring and also for stress testing which is an ideal alternative when the use of a finger sensor is impractical.

We not only provide SpO2 ear clip sensor,and the connector can be customized as well.Such as [Multi leads EEG ECG monitoring electrode cable](#),which with 8 channel active eeg electrodes cable and eeg passive cable.


Any demands of this SpO2 Probe Sensor Ear Clip with audio jack male cable,please contact us.

## Product Photo:





## **Company Info. Overview**



## About Us

10+ Years Experienced Professional Manufacturer of Customized Cables.



2000 M<sup>2</sup>  
Factory space with 10 years  
of production experience



100+  
Employees



OEM/ODM  
Support cable customized



TOP 500  
Bands approved  
manufacturer



## Certificate

We followed international ISO management Standard to make our custom cables, medical cables and chargers with good quality and best price.



## FAQ

### **Q1: Can I start a sample order before I order more?**

A: Sure, Heymed provide free sample if we have stock, customized sample need to be charged setup cost. We appreciate you asking us for a sample to check our quality.

### **Q2: What payment methods do you accept?**

A: PayPal, T/T, Bank Transfer, Western Union and L/C

### **Q3: How is your factory doing regarding quality control?**

A: Quality is priority. QC department with professional quality assurance specialist attaches great importance to quality control from the very beginning to the very end. Our factory has obtained Rohs, SGS, CE FCC, ISO9001:2008 authentication. Etc

### **Q4: Factory? Yes! Can I customize the items I like, such as print our own logo or modify the design?**

A: Yes, we are a factory with more than 100 employees. We offer OEM/ODM service. Please contact us or our sales representative for details.

### **Q5: Delivery time and warranty? What shipping service will you use for my products?**

A: Our lead time is around 2-4 weeks and we can offer 12 months warranty from delivery. We use DHL, Fedex, UPS, TNT, EMS as the customer.

### **Q6: Where is your factory located? How can I visit there?**

A: Sure. We are more than happy to welcome you to Dongguan and show you around our workplace. Our factory is located in 3rd. Floor, Building A, No.8 Kangyang 1st Street, Shebei Village, Huangjiang Town, Dongguan City, Guangdong, China.