

Product parameters

Product Name	Monopolar Conductive Reusable silicone patient plate with cable for Adult
Connector	6.3mm audio connector
Material	Silicone
Color	Black
Applied equipments	Ten machine,ESU grounding pad
Function	Medical health services□Patient plate
MOQ	100PCS

These reusable silicon patient plate [negative return electrode ESU grounding plate](#) is widely used in electrosurgery, it is used together with various high-frequency electrosurgical mainframe and RF instrument to form a circuit with the positive pole of high-frequency electrosurgical mainframe,most used in beauty equipment and electrosurgical.

We are the professional medical cable factory,support customized.The neutral electrode negative plate we also have other type,such as [ESU grounding pad neutral electrode with cable](#),it with plastics Lemo connector plug.Customized connector which could suit for different machine to meet your requirements.

Product Photo:





Company Info. Overview



About Us

10+ Years Experienced Professional Manufacturer
of Customized Cables.



2000 M²
Factory space with 10 years
of production experience



100+
Employees



OEM/ODM
Support cable customized



TOP 500
Bands approved
manufacturer



Certificate

We followed international ISO management Standard to make our custom cables,
medical cables and chargers with good quality and best price.



FAQ

Q1: Can I start a sample order before I order more?

A: Sure, Heymed provide free sample if we have stock, customized sample need to be charged setup cost. We appreciate you asking us for a sample to check our quality.

Q2: What payment methods do you accept?

A: PayPal, T/T, Bank Transfer, Western Union and L/C

Q3: How is your factory doing regarding quality control?

A: Quality is priority. QC department with professional quality assurance specialist attaches great importance to quality control from the very beginning to the very end. Our factory has obtained Rohs, SGS, CE FCC, ISO9001:2008 authentication. Etc

Q4: Factory? Yes! Can I customize the items I like, such as print our own logo or modify the design?

A: Yes, we are a factory with more than 100 employees. We offer OEM/ODM service. Please contact us or our sales representative for details.

Q5: Delivery time and warranty? What shipping service will you use for my products?

A: Our lead time is around 2-4 weeks and we can offer 12 months warranty from delivery. We use DHL, Fedex, UPS, TNT, EMS as the customer.

Q6: Where is your factory located? How can I visit there?

A: Sure. We are more than happy to welcome you to Dongguan and show you around our workplace. Our factory is located in 3rd. Floor, Building A, No.8 Kangyang 1st Street, Shebei Village, Huangjiang Town, Dongguan City, Guangdong, China.