

Product name	Customizable DC 2.35mm Male to DC 2.35mm Female Extension Cable Dongguan Certified Medical Manufacturer
application	Stimulation machine, physical therapy instrument
length	10cm, 20cm, 50cm, 100cm or customized
color	Black, Gray, white, black and customized
Conductor material	Tinned copper
Package	Individually packaged

Product Information:


This DC 2.35mm Male to DC 2.35mm Female Extension Cable is ideal for connecting or extending low-voltage power to devices such as medical equipment, wireless transmitters, audio systems, or TENS/EMS machines. The precise 2.35mm barrel plugs ensure a snug and secure fit, preventing accidental disconnections.

Manufactured by a professional cable factory in Dongguan, China, the cable is available in various lengths, colors, and jacket materials (PVC/TPU) to suit different environments. The pure copper conductor ensures excellent conductivity and stable power transmission, making it an ideal choice for OEM customization.

For those seeking alternative specifications, our [Physiotherapy Lead Wire DC 2.35mm Male to Stopper Medical Cable with Metal Shell](#) offers similar reliability for devices requiring a larger connector, such as certain medical monitors or professional audio setups. Like the 2.35mm variant, it features customizable lengths and durable jacket materials. Additionally, our [DC3.5 Male Plug 2 in 1 Ring - Ended Physiotherapy Lead Wire](#) is designed for compact electronics like portable diagnostic tools, with the same pure copper construction and secure plug design to ensure stable power transmission.

Whether you need short jumper cables or longer power extension cords, this product—along with our broader range of connector solutions—offers flexible, safe, and reliable performance in a compact form.





Certification and Compliance:

This cable meets strict standards to ensure the highest quality and safety levels in the medical field:

- **ISO 13485:** Certification ensures compliance with international standards for medical device quality management systems.
- **ISO 9001:** Ensure that products are manufactured under a sound quality management system.
- **FDA Approved:** The product is registered with the U.S. Food and Drug Administration and meets its medical device standards.
- **CE MDR certification:** Complies with the EU Medical Device Regulation (MDR) to ensure safety and effectiveness for medical use.

Company information. Overview



About Us

10+ Years Experienced Professional Manufacturer of Customized Cables.



2000 M²
Factory space with 10years of production experience



100+
Employees



OEM/ODM
Support cable customized



TOP 500
Bands approved manufacturer



Certificate

We followed international ISO management Standard to make our custom cables, medical cables and chargers with good quality and best price.



ISO 13485

FCC

CE

ROHS



UKCA

EPR

EPR

ISO 9001

FAQ

Q1: Can I start a sample order before ordering more?

A: Of course, Heymed will provide free samples if we have them in stock, customized samples require installation fees. Thank you for asking us for samples to check our quality.

Q2: What payment methods do you accept?

A: PayPal, T/T, bank transfer, Western Union and L/C

Q3: How does your factory do in terms of quality control?

Answer: Quality is priority. The QC department with professional quality assurance experts attaches great importance to quality control from beginning to end. Our factory has obtained Rohs, SGS, CE FCC, ISO9001:2008 certification. ETC

Q4: Factory? Yes! Can I customize the items I like, such as printing our own logo or modifying the design?

A: Yes, we are a factory with more than 100 employees. We provide OEM/ODM services. Please contact us or our sales representative for details.

Q5: Delivery time and warranty? What shipping service will you use to ship my product?

A: Our delivery time is about 2-4 weeks, and we can provide 12 months warranty from delivery. We use DHL, Fedex, UPS, TNT, EMS as customers.

Q6: Where is your factory located? How can I visit there?

Answer: Of course. We are very happy to welcome you to Dongguan and show you our workplace. Our factory is located in the third. Building A, No. 8, Kangyang 1st Street, Shebei Village, Huangjiang Town, Dongguan City, Guangdong Province, China