

Product parameters

| | |
|--------------------|--|
| Product Name | Customized 4PIN Lemo metal female connector to PH2.0-4PIN terminal physiotherapy cable |
| Connector | 4pin metal LEMO connector,PH2.0-4PIN terminal |
| Cable Length | 2.5M,1M,1.8M or customized |
| Cable Color | Black or customized |
| Applied equipments | EEG, ECG,EMG machine |
| Function | Transferring signal,convenience |
| MOQ | 1PCS |

4PIN Remo Metal Female to PH2.0-4PIN Terminal Physiotherapy Cable combines the safety, reliability and efficiency of terminals with easy, fast and safe plugging and unplugging operations, and will not dislodge the plug from the socket by pulling the cable, which plays an active and important role in the manufacturing industry, the medical industry, and aerospace and other fields. Such as [aviation plug waterproofing](#), and [physical therapy monitoring equipment in-unit connection](#), and [computer in-unit cable New energy automobile wiring](#) and so on.

In addition, we also support custom Multi-pin lemo connector to adapt Compatible with the relative equivalent of other connectors applied to the computer internal line of the new energy vehicle wiring and the sound equipments and ecg cable and so on ,for example, [FGG 1B 8Pin Metal LEMO Connector to 6Pin Push Pull Self Locking Aviation Head Cable](#), and [1 in 2 button electrode Remo treatment wire electrode pin lemo electrode wire](#), and [4Pin Plastic LEMO Connector to Electrode Male Pin Cable for TENS](#)

Product Photo:





Company Info. Overview



About Us

10+ Years Experienced Professional Manufacturer of Customized Cables.



2000 M²
Factory space with 10 years
of production experience



100+
Employees



OEM/ODM
Support cable customized



TOP 500
Bands approved
manufacturer



Certificate

We followed international ISO management Standard to make our custom cables, medical cables and chargers with good quality and best price.



FAQ

Q1: Can I start a sample order before I order more?

A: Sure, Heymed provide free sample if we have stock, customized sample need to be charged setup cost. We appreciate you asking us for a sample to check our quality.

Q2: What payment methods do you accept?

A: PayPal, T/T, Bank Transfer, Western Union and L/C

Q3: How is your factory doing regarding quality control?

A: Quality is priority. QC department with professional quality assurance specialist attaches great importance to quality control from the very beginning to the very end. Our factory has obtained Rohs, SGS, CE FCC, ISO9001:2008 authentication. Etc

Q4: Factory? Yes! Can I customize the items I like, such as print our own logo or modify the design?

A: Yes, we are a factory with more than 100 employees. We offer OEM/ODM service. Please contact us or our sales representative for details.

Q5: Delivery time and warranty? What shipping service will you use for my products?

A: Our lead time is around 2-4 weeks and we can offer 12 months warranty from delivery. We use DHL, Fedex, UPS, TNT, EMS as the customer.

Q6: Where is your factory located? How can I visit there?

A: Sure. We are more than happy to welcome you to Dongguan and show you around our workplace. Our factory is located in 3rd. Floor, Building A, No.8 Kangyang 1st Street, Shebei Village, Huangjiang Town, Dongguan City, Guangdong, China.