

Product parameters

Product Name	Customized 5Pin Lemo Plastic Plug to 4.0mm Female Electrode Snap Connector ECG Cable for Medical Monitoring Dongguan Manufacturer
Connector	Plastic LEMO Connector,4.0mm ECG Female Snap Button
Cable Length	1m or customized
Cable Color	Grey or customized
Applied equipments	EEG, ECG,EMG
Function	Transferring signal
MOQ	100PCS

Our 5Pin Lemo Plastic Plug to 4.0mm Snap ECG Electrode Cable is engineered for reliable performance in medical diagnostic and monitoring applications such as ECG, EMG, or biofeedback systems. The Lemo-style plastic connector ensures a secure and precise interface with your monitoring equipment, while the 4.0mm snap connector offers wide compatibility with reusable or disposable electrode pads. For those seeking alternative configurations, our [USB Type C to 4.0mm Female Snap Cable with 2 Leads Wire](#) (designed for compact devices with enhanced durability) and [6Pin Lemo Plastic Plug to Dual 3.5mm Magnetic Electrode Snap Connector with 2 Lead Wires](#) (suitable for multi-channel monitoring systems) are also popular choices, both manufactured with the same ISO13485-certified quality standards.


Manufactured in Dongguan, China, our ISO13485-certified factory maintains strict quality control to meet the demands of global healthcare markets. We support OEM/ODM services for customization in connector types, cable length, color, labeling, and packaging. This product is widely used in hospitals, clinics, home health devices, and research labs.

Product Photo:





Company Info. Overview



About Us

10+ Years Experienced Professional Manufacturer of Customized Cables.



2000 M²
Factory space with 10 years
of production experience



100+
Employees



OEM/ODM
Support cable customized



TOP 500
Bands approved
manufacturer



Certificate

We followed international ISO management Standard to make our custom cables, medical cables and chargers with good quality and best price.



FAQ

Q1: Can I start a sample order before I order more?

A: Sure, Heymed provide free sample if we have stock, customized sample need to be charged setup cost. We appreciate you asking us for a sample to check our quality.

Q2: What payment methods do you accept?

A: PayPal, T/T, Bank Transfer, Western Union and L/C

Q3: How is your factory doing regarding quality control?

A: Quality is priority. QC department with professional quality assurance specialist attaches great importance to quality control from the very beginning to the very end. Our factory has obtained Rohs, SGS, CE FCC, ISO9001:2008 authentication. Etc

Q4: Factory? Yes! Can I customize the items I like, such as print our own logo or modify the design?

A: Yes, we are a factory with more than 100 employees. We offer OEM/ODM service. Please contact us or our sales representative for details.

Q5: Delivery time and warranty? What shipping service will you use for my products?

A: Our lead time is around 2-4 weeks and we can offer 12 months warranty from delivery. We use DHL, Fedex, UPS, TNT, EMS as the customer.

Q6: Where is your factory located? How can I visit there?

A: Sure. We are more than happy to welcome you to Dongguan and show you around our workplace. Our factory is located in 3rd. Floor, Building A, No.8 Kangyang 1st Street, Shebei Village, Huangjiang Town, Dongguan City, Guangdong, China.