

Product parameters

Product Name	Spring Loaded Pogo 9pins Connector to Round Ring with 5 Lead Wires
Connector	3.5mm/4.0mm female snap to USB C plug
Cable Length	30cm or customized
Cable Color	Black or customized
Function	TENS EMS Transmission/Massager ECG/EKG/EEG/EMG Adapter Cable
MOQ	100PCS

This 9pin spring loaded magnetic pogo pin connector to round ring terminal ECG electrode cable is widely used in medical industry, which is made up of pogo pin connector, crimping terminal with 5 lead wires, can also be used for EEG ECG machine. Besides, we support OEM ODM services for all of our cable products with medical grade shielded wire (TPU material), such as [Customized 12Pin Din Connector to Test Clip Y Splitter Cable](#)

As an ISO13485 medical device management system certification manufacturer, we have many years of experience in producing [ECG EKG EEG EMG cables](#) and other [electrode medical cable accessories](#).


Meanwhile, we have decades of wire customization experience in [Multi Leads EEG ECG Monitoring Electrode Cable](#) and have sufficient cable customized experience to meet any customization needs of our customers.

Product Photo:





Company Info. Overview



About Us

10+ Years Experienced Professional Manufacturer of Customized Cables.



2000 M²
Factory space with 10 years
of production experience



100+
Employees



OEM/ODM
Support cable customized



TOP 500
Bands approved
manufacturer



Certificate

We followed international ISO management Standard to make our custom cables, medical cables and chargers with good quality and best price.



ISO13485

FCC

CE

RoHS



UKCA

EPR

EPR

ISO9001

FAQ

Q1: Can I start a sample order before I order more?

A: Sure, Heymed provide free sample if we have stock, customized sample need to be charged setup cost. We appreciate you asking us for a sample to check our quality.

Q2: What payment methods do you accept?

A: PayPal, T/T, Bank Transfer, Western Union and L/C

Q3: How is your factory doing regarding quality control?

A: Quality is priority. QC department with professional quality assurance specialist attaches great importance to quality control from the very beginning to the very end. Our factory has obtained Rohs, SGS, CE FCC, ISO9001:2008 authentication. Etc

Q4: Factory? Yes! Can I customize the items I like, such as print our own logo or modify the design?

A: Yes, we are a factory with more than 100 employees. We offer OEM/ODM service. Please contact us or our sales representative for details.

Q5: Delivery time and warranty? What shipping service will you use for my products?

A: Our lead time is around 2-4 weeks and we can offer 12 months warranty from delivery. We use DHL, Fedex, UPS, TNT, EMS as the customer.

Q6: Where is your factory located? How can I visit there?

A: Sure. We are more than happy to welcome you to Dongguan and show you around our workplace. Our factory is located in 3rd. Floor, Building A, No.8 Kangyang 1st Street, Shebei Village, Huangjiang Town, Dongguan City, Guangdong, China.