

Product parameters

Product name	Lemo 4P Self-Locking Connector with Dual 2mm Electrode Lead Wire with Plastic Protect cover
connector	3.5mm/4.0mm female and USB Type C Male
Cable length	120cm or customized
Cable color	white black or customized
Function	TENS EMS Transmission/Massager ECG/EKG/EEG/EMG Adapter Cable
Minimum order quantity	500pcs

Product Feature:

LEMO B Series modular push-pull connectors offer quick and secure latching for a variety of end applications, 2MM Electrode Pin with Protect Cover also can protect the pin and comply with Medical Standard.

We can make many types [medical cable with Lemo Connector](#), like Ecg Snap Cable, Electrode Pin Cable, Alligator Clip Cable, Banana Plug Cable, Magnetic Snap Cable and so on.

Except Metal Lemo Connector, we also have redel plastic connector with ECG electrode snap cable, [ECG EKG EMG EMC Tens Lead Wire](#).

Heymed Located in Dongguan, ISO 13485&ISO 9001 certified custom cable assembly, we can produce ecg snap cable, negative plate and other cable assemblies.

Product Photos:





Company information. Overview



About Us

10+ Years Experienced Professional Manufacturer
of Customized Cables.



2000 M²
Factory space with 10 years
of production experience



100+
Employees



OEM/ODM
Support cable customized



TOP 500
Bands approved
manufacturer



Certificate

We followed international ISO management Standard to make our custom cables,
medical cables and chargers with good quality and best price.



FAQ

Q1: Can I start a sample order before ordering more?

A: Of course, Heymed provides free samples if we have them in stock, customized samples require installation fees. Thank you for asking us for samples to check our quality.

Q2: What payment methods do you accept?

A: PayPal, T/T, bank transfer, Western Union and L/C

Q3: How does your factory do in terms of quality control?

Answer: Quality is priority. The QC department with professional quality assurance experts attaches great importance to quality control from the beginning to the end. Our factory has obtained Rohs, SGS, CE FCC, ISO9001:2008 certification. ETC

Q4: Factory? Yes! Can I customize the items I like, such as printing our own logo or modifying the design?

A: Yes, we are a factory with more than 100 employees. We provide OEM/ODM services. Please contact us or our sales representative for details.

Q5: Delivery time and warranty? What shipping service will you use to ship my product?

A: Our delivery time is about 2-4 weeks, and we can provide a 12-month warranty from delivery. We use DHL, Fedex, UPS, TNT, EMS as customers.

Q6: Where is your factory located? How can I visit there?

Answer: Of course. We are very happy to welcome you to Dongguan and show you our workplace. Our factory is located in the third. Building A, No. 8, Kangyang 1st Street, Shebei Village, Huangjiang Town, Dongguan City, Guangdong Province, China