

## Product parameters

Product Name	5 Poles 3.5mm Audio Jack to 4.0mm Medical Electrode Snap cable Lead Wire
Connector	3.5mm/4.0mm female snap to audio jack
Cable Length	120cm or customized
Cable Color	White Black or customized
Function	TENS EMS Transmission/Massager ECG/EKG/EEG/EMG Adapter Cable
MOQ	100PCS

As an ISO13485 medical device management system certification manufacturer,we have many years of experience in producing [ECG EKG EEG EMG cables](#) and other [electrode medical cable accessories](#).

This Anti static banana plug to ECG snap medical cable is made up of elbow banana plug and 4.0mm ecg female snap button,can used for EEG ECG machine.Besides,we support OEM ODM services for all of our cable products with medical grade shielded wire(TPU material),such as [Electrode Female Snap to Banana Plug Male ECG Cable](#).


Meanwhile,we have decades of wire customization experience in [Multi Leads EEG ECG Monitoring Electrode Cable](#) and have sufficient cable customized experience to meet any customization needs of our customers.

## Product Photo:





## Company Info. Overview



## About Us

10+ Years Experienced Professional Manufacturer  
of Customized Cables.



2000 M<sup>2</sup>  
Factory space with 10 years  
of production experience



100+  
Employees



OEM/ODM  
Support cable customized



TOP 500  
Bands approved  
manufacturer



## Certificate

We followed international ISO management Standard to make our custom cables,  
medical cables and chargers with good quality and best price.



# FAQ

## **Q1: Can I start a sample order before I order more?**

A: Sure, Heymed provide free sample if we have stock, customized sample need to be charged setup cost. We appreciate you asking us for a sample to check our quality.

## **Q2: What payment methods do you accept?**

A: PayPal, T/T, Bank Transfer, Western Union and L/C

## **Q3: How is your factory doing regarding quality control?**

A: Quality is priority. QC department with professional quality assurance specialist attaches great importance to quality control from the very beginning to the very end. Our factory has obtained Rohs, SGS, CE FCC, ISO9001:2008 authentication. Etc

## **Q4: Factory? Yes! Can I customize the items I like, such as print our own logo or modify the design?**

A: Yes, we are a factory with more than 100 employees. We offer OEM/ODM service. Please contact us or our sales representative for details.

## **Q5: Delivery time and warranty? What shipping service will you use for my products?**

A: Our lead time is around 2-4 weeks and we can offer 12 months warranty from delivery. We use DHL, Fedex, UPS, TNT, EMS as the customer.

## **Q6: Where is your factory located? How can I visit there?**

A: Sure. We are more than happy to welcome you to Dongguan and show you around our workplace. Our factory is located in 3rd. Floor, Building A, No.8 Kangyang 1st Street, Shebei Village, Huangjiang Town, Dongguan City, Guangdong, China.