

## Product parameters


Product Name	Factory Price in Custom M12 3P Aviation connector to Stainless steel negative Plate for Beauty Salon General Purpose
Connector	M12 3P Aviation connector
Material	PVC Aviation connector+Stainless Steel
Color	Black,Custom
Applied equipments	Computers, radar, power lines
Function	Medical health services□Safe operation of aircraft, telex data, signal transmission
MOQ	100PCS

Aviation plug shell is usually made of aluminum alloy, nickel-plated, copper and other materials, mostly used in military, railroad, electric power and other industries. Performance materials are very durable, therefore, surgical operating rooms are also often used to stainless steel negative plate connected to the [2PIN Metal Lemo Plug as Surgical Accessories](#) . In addition, [electric negative plate connected to audio connector](#) is also commonly used in ESU floor consumables patient board electrotome accessories!

Our customized products are not only limited to one field, we accept different materials, different connectors and other customized specifications, which are very effective in medical and other fields, such as [Silicone Electrosurgical Negative Plate](#), [ESU Grounding Pad Negative Plate](#) and [Steel Negative Plate with Lemo Plug](#) and [DuPont connectors to Snap ecg cable](#) and so on.

## Product Photo:

## Company Info. Overview



## About Us

10+ Years Experienced Professional Manufacturer  
of Customized Cables.



2000 M<sup>2</sup>  
Factory space with 10 years  
of production experience



100+  
Employees



OEM/ODM  
Support cable customized



TOP 500  
Bands approved  
manufacturer



## Certificate

We followed international ISO management Standard to make our custom cables,  
medical cables and chargers with good quality and best price.



## FAQ

### **Q1: Can I start a sample order before I order more?**

A: Sure, Heymed provide free sample if we have stock, customized sample need to be charged setup cost. We appreciate you asking us for a sample to check our quality.

### **Q2: What payment methods do you accept?**

A: PayPal, T/T, Bank Transfer, Western Union and L/C

### **Q3: How is your factory doing regarding quality control?**

A: Quality is priority. QC department with professional quality assurance specialist attaches great importance to quality control from the very beginning to the very end. Our factory has obtained Rohs, SGS, CE FCC, ISO9001:2008 authentication. Etc

### **Q4: Factory? Yes! Can I customize the items I like, such as print our own logo or modify the design?**

A: Yes, we are a factory with more than 100 employees. We offer OEM/ODM service. Please contact us or our sales representative for details.

### **Q5: Delivery time and warranty? What shipping service will you use for my products?**

A: Our lead time is around 2-4 weeks and we can offer 12 months warranty from delivery. We use DHL, Fedex, UPS, TNT, EMS as the customer.

### **Q6: Where is your factory located? How can I visit there?**

A: Sure. We are more than happy to welcome you to Dongguan and show you around our workplace. Our factory is located in 3rd. Floor, Building A, No.8 Kangyang 1st Street, Shebei Village, Huangjiang Town, Dongguan City, Guangdong, China.