

## Product parameters

Product Name	RJ45 Gigabit Ethernet Cable Industrial Digital Camera Machine Vision Cable Cord
Connector	RJ45 8P8C male to female,Cat 6
Cable Length	30cm or customized
Cable Color	Black or customized
Applied equipments	CCD camera,Machine vision
Function	Data transmission,Transfer reliability
MOQ	100PCS

This Gigabit ethernet cable industrial digital camera machine vision video cords with screws mounting lock,widely used for wiring of mobile robots, robotic arms, machine tools, automation equipment, tank chains, and high-speed mobile parts.Adopting high-strength bending and wear-resistant PVC material and super flexible heat-resistant PVC material, the bending life can reach over 30 million times; Waterproof, oil resistant, heat resistant (80 °C), UV resistant, flame retardant.Compliant with UL/cUL mandatory safety specification certification.

Also,we also have RJ45 8P8C Cat5 Cat5e Cat6 male to female ethernet extension cable, is perfect for extend your ethernet connection to reach a router or HDTV,home theater and protect the computer network port from constant plug and unplug as well as with high speed upload&download data transfer for server applications.Beside,we have similar ethernet network cable like [RJ12 6P6C male to female telephone cable](#).

## Product Photo:









## **Company Info. Overview**



## About Us

10+ Years Experienced Professional Manufacturer  
of Customized Cables.



2000 M<sup>2</sup>  
Factory space with 10 years  
of production experience



100+  
Employees



OEM/ODM  
Support cable customized



TOP 500  
Bands approved  
manufacturer



## Certificate

We followed international ISO management Standard to make our custom cables,  
medical cables and chargers with good quality and best price.



# FAQ

## **Q1: Can I start a sample order before I order more?**

A: Sure, Heymed provide free sample if we have stock, customized sample need to be charged setup cost. We appreciate you asking us for a sample to check our quality.

## **Q2: What payment methods do you accept?**

A: PayPal, T/T, Bank Transfer, Western Union and L/C

## **Q3: How is your factory doing regarding quality control?**

A: Quality is priority. QC department with professional quality assurance specialist attaches great importance to quality control from the very beginning to the very end. Our factory has obtained Rohs, SGS, CE FCC, ISO9001:2008 authentication. Etc

## **Q4: Factory? Yes! Can I customize the items I like, such as print our own logo or modify the design?**

A: Yes, we are a factory with more than 100 employees. We offer OEM/ODM service. Please contact us or our sales representative for details.

## **Q5: Delivery time and warranty? What shipping service will you use for my products?**

A: Our lead time is around 2-4 weeks and we can offer 12 months warranty from delivery. We use DHL, Fedex, UPS, TNT, EMS as the customer.

## **Q6: Where is your factory located? How can I visit there?**

A: Sure. We are more than happy to welcome you to Dongguan and show you around our workplace. Our factory is located in 3rd. Floor, Building A, No.8 Kangyang 1st Street, Shebei Village, Huangjiang Town, Dongguan City, Guangdong, China.