

## Product parameters

Product Name	Nylon Braided Type C to USB 2.0 B Printer Cable for Laptop Camera Hard Drive
Connector	Type C Male to USB B Male Connector
Cable Length	30cm or customized
Cable Color	Black or customized
Applied equipments	Laptop,Notebook,Samsung Phone
Function	High speed data transfer,sync,PD fast charging
MOQ	100PCS


This USB C printer cable is compatible for laptop camera hard drive,with high-speeds data transfer,can provide more stable data transfer than a WIFI connection. It supports high-speeds data transfer/sync up to 480 Mbps.Adopt durable material, featuring a nylon braided fiber jacket, the USB C to USB B cable is corrosion-resistant. The aluminum housing makes the printer cable bend freely 10000+ times, more durable, and sturdier for a longer lifespan.

Meanwhile,we also have [type c high speed data syncing PD fast charging cable](#) used for charging and data transfer. This USB C printer cable is compatible for laptop camera hard drive.

If you have any demands of this printer cable or other USB charging cable,please feel free to contact us.

## Product Photo:









## Company Info. Overview



## About Us

10+ Years Experienced Professional Manufacturer  
of Customized Cables.



2000 M<sup>2</sup>  
Factory space with 10 years  
of production experience



100+  
Employees



OEM/ODM  
Support cable customized



TOP 500  
Bands approved  
manufacturer



## Certificate

We followed international ISO management Standard to make our custom cables,  
medical cables and chargers with good quality and best price.



ISO13485

FCC

CE

ROHS



UKCA

EPR

EPR

ISO9001

# FAQ

## **Q1: Can I start a sample order before I order more?**

A: Sure, Heymed provide free sample if we have stock, customized sample need to be charged setup cost. We appreciate you asking us for a sample to check our quality.

## **Q2: What payment methods do you accept?**

A: PayPal, T/T, Bank Transfer, Western Union and L/C

## **Q3: How is your factory doing regarding quality control?**

A: Quality is priority. QC department with professional quality assurance specialist attaches great importance to quality control from the very beginning to the very end. Our factory has obtained Rohs, SGS, CE FCC, ISO9001:2008 authentication. Etc

## **Q4: Factory? Yes! Can I customize the items I like, such as print our own logo or modify the design?**

A: Yes, we are a factory with more than 100 employees. We offer OEM/ODM service. Please contact us or our sales representative for details.

## **Q5: Delivery time and warranty? What shipping service will you use for my products?**

A: Our lead time is around 2-4 weeks and we can offer 12 months warranty from delivery. We use DHL, Fedex, UPS, TNT, EMS as the customer.

## **Q6: Where is your factory located? How can I visit there?**

A: Sure. We are more than happy to welcome you to Dongguan and show you around our workplace. Our factory is located in 3rd. Floor, Building A, No.8 Kangyang 1st Street, Shebei Village, Huangjiang Town, Dongguan City, Guangdong, China.