

## Product parameters

Product Name	M5 5pin connector to ECG grabber clip and male pin electrode cable
Connector	2.0 electrode pin male/ ecg grabber clip/M5 waterproof plug
Cable Length	30cm or customized
Cable Color	Medical gray or customized
Function	TENS EMS Transmission
MOQ	100PCS

This OEM ODM ECG grabber clip cable with M5 5pin IP67 waterproof connector and electrode pin which is used for ECG EKG machine.


Heymed as a professional [customized medical ecg eeg ekg emg cable](#) manufacturer, could according to customer's different requirements to made the customized cable they need. Such as the [multi leads EEG ECG monitoring electrode cable](#), with material of high medical grade shielded wire and 8 channel passive eeg electrodes cable. Meanwhile, we have decades of wire customization experience in [spring spiral coiled cable](#) and have sufficient cable customized experience to meet any customization needs of our customers.

## Product Photo:





**Company Info. Overview**



## About Us

10+ Years Experienced Professional Manufacturer of Customized Cables.



2000 M<sup>2</sup>  
Factory space with 10 years  
of production experience



100+  
Employees



OEM/ODM  
Support cable customized



TOP 500  
Bands approved  
manufacturer



## Certificate

We followed international ISO management Standard to make our custom cables, medical cables and chargers with good quality and best price.



# FAQ

## **Q1: Can I start a sample order before I order more?**

A: Sure, Heymed provide free sample if we have stock, customized sample need to be charged setup cost. We appreciate you asking us for a sample to check our quality.

## **Q2: What payment methods do you accept?**

A: PayPal, T/T, Bank Transfer, Western Union and L/C

## **Q3: How is your factory doing regarding quality control?**

A: Quality is priority. QC department with professional quality assurance specialist attaches great importance to quality control from the very beginning to the very end. Our factory has obtained Rohs, SGS, CE FCC, ISO9001:2008 authentication. Etc

## **Q4: Factory? Yes! Can I customize the items I like, such as print our own logo or modify the design?**

A: Yes, we are a factory with more than 100 employees. We offer OEM/ODM service. Please contact us or our sales representative for details.

## **Q5: Delivery time and warranty? What shipping service will you use for my products?**

A: Our lead time is around 2-4 weeks and we can offer 12 months warranty from delivery. We use DHL, Fedex, UPS, TNT, EMS as the customer.

## **Q6: Where is your factory located? How can I visit there?**

A: Sure. We are more than happy to welcome you to Dongguan and show you around our workplace. Our factory is located in 3rd. Floor, Building A, No.8 Kangyang 1st Street, Shebei Village, Huangjiang Town, Dongguan City, Guangdong, China.