

Product parameters

Product Name	Plastic LEMO Push-Pull Connectors to Electrode Male Pin Cable
Connector	Plastic LEMO connector,2.0mm male pin
Cable Length	30cm or customized
Cable Color	Black or customized
Applied equipments	EEG, ECG,EMG
Function	Transferring signal
MOQ	100PCS

This customized 4Pin plastics Lemo connector to electrode male pin [ECG/EKG cable](#),is widely used in medical industry,such as ECG EEG EKG EMG machine or TENS device,and this Lemo 4pin self-locking male connector to 2.0mm male Din cable can make from different wire material,such as TPU medical grade shielded wire.

In addition,we also have other similar medical din cable such as [Elbow Type C Male to 2.0mm Electrode 4Pin Male Lead Wire](#) and [USB C Male to 2.0mm Electrode Male Pin Lead Wire with Spring Spiral Coiled Cord Cable](#).

As a professional medical ecg eeg ekg emg cable manufacturer,we have decades of wire customization experience and have sufficient cable customized experience to meet any different customization needs of our customers,for example [Multi Leads EEG ECG Monitoring Electrode Cable](#).

Product Photo:





About Us

10+ Years Experienced Professional Manufacturer
of Customized Cables.



2000 M²
Factory space with 10 years
of production experience



100+
Employees



OEM/ODM
Support cable customized



TOP 500
Bands approved
manufacturer



Certificate

We followed international ISO management Standard to make our custom cables,
medical cables and chargers with good quality and best price.



FAQ

Q1: Can I start a sample order before I order more?

A: Sure, Heymed provide free sample if we have stock, customized sample need to be charged setup cost. We appreciate you asking us for a sample to check our quality.

Q2: What payment methods do you accept?

A: PayPal, T/T, Bank Transfer, Western Union and L/C

Q3: How is your factory doing regarding quality control?

A: Quality is priority. QC department with professional quality assurance specialist attaches great importance to quality control from the very beginning to the very end. Our factory has obtained Rohs, SGS, CE FCC, ISO9001:2008 authentication. Etc

Q4: Factory? Yes! Can I customize the items I like, such as print our own logo or modify the design?

A: Yes, we are a factory with more than 100 employees. We offer OEM/ODM service. Please contact us or our sales representative for details.

Q5: Delivery time and warranty? What shipping service will you use for my products?

A: Our lead time is around 2-4 weeks and we can offer 12 months warranty from delivery. We use DHL, Fedex, UPS, TNT, EMS as the customer.

Q6: Where is your factory located? How can I visit there?

A: Sure. We are more than happy to welcome you to Dongguan and show you around our workplace. Our factory is located in 3rd. Floor, Building A, No.8 Kangyang 1st Street, Shebei Village, Huangjiang Town, Dongguan City, Guangdong, China.