

Product parameters

Product Name	RJ45 Male to Female Ethernet LAN Network Extension Cable for PC Laptop
Connector	RJ45 8P8C male to female connector with switch control
Cable Length	30cm or customized
Cable Color	Black or customized
Applied equipments	HDTV,home theater,DVD player,projector,PS3, other devices
Function	Data transmission,sync
MOQ	100PCS

RJ45 8P8C Cat5 Cat5e Cat6 male to female ethernet extension cable is perfect for extend your ethernet connection to reach a router or HDTV,home theater and protect the computer network port from constant plug and unplug as well as with high speed upload&download data transfer for server applications.Beside,we have similar ethernet network cable like [RJ12 6P6C male to female telephone cable](#).

In the field of network cable production, we have many years of production and research&development experience, and have our own molds in various cable. In addition, we also have other wire product lines, such as USB cable, medical cable, and computer cable.For the USB cable,the most popular cables we recommand is [USB 3.0 A male to female extension data cable](#).

Product Photo:





Company Info. Overview



About Us

10+ Years Experienced Professional Manufacturer of Customized Cables.



2000 M²
Factory space with 10 years
of production experience



100+
Employees



OEM/ODM
Support cable customized



TOP 500
Bands approved
manufacturer



Certificate

We followed international ISO management Standard to make our custom cables, medical cables and chargers with good quality and best price.



ISO13485

FCC

CE

RoHS



UKCA

EPR

EPR

ISO9001

FAQ

Q1: Can I start a sample order before I order more?

A: Sure, Heymed provide free sample if we have stock, customized sample need to be charged setup cost. We appreciate you asking us for a sample to check our quality.

Q2: What payment methods do you accept?

A: PayPal, T/T, Bank Transfer, Western Union and L/C

Q3: How is your factory doing regarding quality control?

A: Quality is priority. QC department with professional quality assurance specialist attaches great importance to quality control from the very beginning to the very end. Our factory has obtained Rohs, SGS, CE FCC, ISO9001:2008 authentication. Etc

Q4: Factory? Yes! Can I customize the items I like, such as print our own logo or modify the design?

A: Yes, we are a factory with more than 100 employees. We offer OEM/ODM service. Please contact us or our sales representative for details.

Q5: Delivery time and warranty? What shipping service will you use for my products?

A: Our lead time is around 2-4 weeks and we can offer 12 months warranty from delivery. We use DHL, Fedex, UPS, TNT, EMS as the customer.

Q6: Where is your factory located? How can I visit there?

A: Sure. We are more than happy to welcome you to Dongguan and show you around our workplace. Our factory is located in 3rd. Floor, Building A, No.8 Kangyang 1st Street, Shebei Village, Huangjiang Town, Dongguan City, Guangdong, China.