

Product parameters

Product Name	High Quality RJ50 Cat5 Male to Male Ethernet Extension Cable
Connector	RJ50 10P10C male to male connector
Cable Length	30cm or customized
Cable Color	Black or customized
Applied equipments	Scanning Code Guns,Laser Printing Equipment,Industrial Control Equipment
Function	Data transmission,sync
MOQ	100PCS

This customized Cat5 RJ50 10P10C male to male [ethernet extension cable](#) with high quality TPU material and with better folding resistant design which is perfect for extend your ethernet connection to reach a router or HDTV,home theater and protect the computer network port from constant plug and unplug as well as with high speed upload&download data transfer for server applications.We also have the ethernet industrial camera cable,such as [RJ45 industrial digital camera machine vision video cable](#).

In the field of network cable production, we have many years of production and research&development experience, and have our own molds in various cable. In addition, we also have other wire product lines, such as USB cable, medical cable, and computer cable and have similar ethernet network cable like [RJ12 6P6C male to female telephone cable](#).

Product Photo:





Company Info. Overview



About Us

10+ Years Experienced Professional Manufacturer of Customized Cables.



2000 M²
Factory space with 10 years
of production experience



100+
Employees



OEM/ODM
Support cable customized



TOP 500
Bands approved
manufacturer



Certificate

We followed international ISO management Standard to make our custom cables, medical cables and chargers with good quality and best price.



FAQ

Q1: Can I start a sample order before I order more?

A: Sure, Heymed provide free sample if we have stock, customized sample need to be charged setup cost. We appreciate you asking us for a sample to check our quality.

Q2: What payment methods do you accept?

A: PayPal, T/T, Bank Transfer, Western Union and L/C

Q3: How is your factory doing regarding quality control?

A: Quality is priority. QC department with professional quality assurance specialist attaches great importance to quality control from the very beginning to the very end. Our factory has obtained Rohs, SGS, CE FCC, ISO9001:2008 authentication. Etc

Q4: Factory? Yes! Can I customize the items I like, such as print our own logo or modify the design?

A: Yes, we are a factory with more than 100 employees. We offer OEM/ODM service. Please contact us or our sales representative for details.

Q5: Delivery time and warranty? What shipping service will you use for my products?

A: Our lead time is around 2-4 weeks and we can offer 12 months warranty from delivery. We use DHL, Fedex, UPS, TNT, EMS as the customer.

Q6: Where is your factory located? How can I visit there?

A: Sure. We are more than happy to welcome you to Dongguan and show you around our workplace. Our factory is located in 3rd. Floor, Building A, No.8 Kangyang 1st Street, Shebei Village, Huangjiang Town, Dongguan City, Guangdong, China.