

## Product parameters

Product Name	Reusable Stainless Steel Adult Dispersive Electrode Grounding Pad
Connector	None Connector
Material	Stainless Steel
Color	Black
Applied equipments	Ten machine,ESU grounding pad
Function	Medical health services□Patient plate,Electrosurgical
MOQ	100PCS

These reusable patient plate [negative return electrode ESU grounding plate](#) is widely used in electrosurgery, it is used together with various high-frequency electrosurgical mainframe and RF instrument to form a circuit with the positive pole of high-frequency electrosurgical mainframe,most used in beauty equipment and electrosurgical.

This stainless steel negative electrode plate,support any customized to connecte any device.The neutral electrode negative plate we also have other type,such as [ESU grounding pad neutral electrode with cable](#),it with plastics Lemo connector plug.Customized connector which could suit for different machine to meet your requirements.We also have [disposable neutral electrode plate](#) for your reference.

## Product Photo:









**Company Info. Overview**



## About Us

10+ Years Experienced Professional Manufacturer of Customized Cables.



2000 M<sup>2</sup>  
Factory space with 10 years  
of production experience



100+  
Employees



OEM/ODM  
Support cable customized



TOP 500  
Bands approved  
manufacturer



## Certificate

We followed international ISO management Standard to make our custom cables, medical cables and chargers with good quality and best price.



ISO13485

FCC

CE

RoHS



UKCA

EPR

EPR

ISO9001

# FAQ

## **Q1: Can I start a sample order before I order more?**

A: Sure, Heymed provide free sample if we have stock, customized sample need to be charged setup cost. We appreciate you asking us for a sample to check our quality.

## **Q2: What payment methods do you accept?**

A: PayPal, T/T, Bank Transfer, Western Union and L/C

## **Q3: How is your factory doing regarding quality control?**

A: Quality is priority. QC department with professional quality assurance specialist attaches great importance to quality control from the very beginning to the very end. Our factory has obtained Rohs, SGS, CE FCC, ISO9001:2008 authentication. Etc

## **Q4: Factory? Yes! Can I customize the items I like, such as print our own logo or modify the design?**

A: Yes, we are a factory with more than 100 employees. We offer OEM/ODM service. Please contact us or our sales representative for details.

## **Q5: Delivery time and warranty? What shipping service will you use for my products?**

A: Our lead time is around 2-4 weeks and we can offer 12 months warranty from delivery. We use DHL, Fedex, UPS, TNT, EMS as the customer.

## **Q6: Where is your factory located? How can I visit there?**

A: Sure. We are more than happy to welcome you to Dongguan and show you around our workplace. Our factory is located in 3rd. Floor, Building A, No.8 Kangyang 1st Street, Shebei Village, Huangjiang Town, Dongguan City, Guangdong, China.