

## Product parameters

|                    |  |
|--------------------|--|
| Product Name       | Electrode Patches Tens Acupuncture Massage EMS Adhesive Gel Pads with Hole |
| Connector          | 2.0mm female connector   |
| Material           | Non-Woven Fabric   |
| Color              | White  |
| Applied equipments | Hospital medical,Dysphagia Machine   |
| Function           | Medical health services,Swallow throat physiotherapy                       |
| MOQ                | 100PCS   |

Our [TENS Unit Adhesive Electrode Pads with 2.0mm Female Connector](#) are pre-gels and do not require additional creams or gels. The durable integral structure allows patients easily removing by pulling up from the leaf tail without damaging the structure.They are companion for most TENS units, or Electrical Muscle Stimulation Machines that use the industry standard 3.5mm Snap-on Connector.

We are the professional medical manufacturer,support customized.The Tens Electrode Pad Replacement Gel Pads we also have other type,such as [Reusable Stainless Steel Negative Plate with Metal Lemo Plug](#),which used for medical health services,patient plate and so on.

## Product Photo:









## **Company Info. Overview**



## About Us

10+ Years Experienced Professional Manufacturer of Customized Cables.



2000 M<sup>2</sup>  
Factory space with 10years of production experience



100+  
Employees



OEM/ODM  
Support cable customized



TOP 500  
Bands approved manufacturer



## Certificate

We followed international ISO management Standard to make our custom cables, medical cables and chargers with good quality and best price.



ISO 13485

FCC

CE

ROHS



UKCA

EPR

EPR

ISO 9001

# FAQ

## **Q1: Can I start a sample order before I order more?**

A: Sure, Heymed provide free sample if we have stock, customized sample need to be charged setup cost. We appreciate you asking us for a sample to check our quality.

## **Q2: What payment methods do you accept?**

A: PayPal, T/T, Bank Transfer, Western Union and L/C

## **Q3: How is your factory doing regarding quality control?**

A: Quality is priority. QC department with professional quality assurance specialist attaches great importance to quality control from the very beginning to the very end. Our factory has obtained Rohs, SGS, CE FCC, ISO9001:2008 authentication. Etc

## **Q4: Factory? Yes! Can I customize the items I like, such as print our own logo or modify the design?**

A: Yes, we are a factory with more than 100 employees. We offer OEM/ODM service. Please contact us or our sales representative for details.

## **Q5: Delivery time and warranty? What shipping service will you use for my products?**

A: Our lead time is around 2-4 weeks and we can offer 12 months warranty from delivery. We use DHL, Fedex, UPS, TNT, EMS as the customer.

## **Q6: Where is your factory located? How can I visit there?**

A: Sure. We are more than happy to welcome you to Dongguan and show you around our workplace. Our factory is located in 3rd. Floor, Building A, No.8 Kangyang 1st Street, Shebei Village, Huangjiang Town, Dongguan City, Guangdong, China.