

Trade Terms: FOB shenzhen/Guangzhou/Hongkong

Production Capacity:1,000,000 pcs per month

Payment : T/T, Paypal, western union

Place of Origin: Dongguan, China

Delivery time: sample lead time 3-7days, mass production is around 15-20 days

Certificates□UL, CE, ROHS, FCC, UKCA

Shipping: By air, by sea or Fedex, DHL, UPS

MOQ:500PCS

---

### **Features:**

- 1.Basic customers require customized plugs angle, which can choose different angle directions, such as 90 degrees, left elbow, right elbow, etc.
2. Tens wires are suitable for travel equipment, electrode wire is easy to operate, and can be used at any time. leads wires are convenience of storage and use.
3. Used in digital machines, slimming massagers, TENS machines, and other health care equipment. leads wires tens can be used for a long time, and are safe, tens leads wires are sturdy and practical.


Similar items:

[90 Degree DC2.35 Plug to 2.0 Electrode Pin ECG Cable](#),and [4Pin Snap-in Plug To 2.0 Electrode Pin](#)

Products Quality Guaranteed 12months+ and RoHS and Reach Compliant & Certification

Hemed has already certified by I S O 13485 Medical devices quality management, I S O 9 0 0 1 Registration for international quality management and I S O 1 4 0 0 1 Registration for environmental management system and Products has Passed UL , CQC,CE, SGS Testing reports





## FAQ

### Q1: Can I start a sample order before I order more?

A: Sure, Heymed provide free sample if we have stock, customized sample need to be charged setup cost. We appreciate you asking us for a sample to check our quality.

### Q2: What payment methods do you accept?

A: PayPal, T/T, Bank Transfer, Western Union and L/C

**Q3: How is your factory doing regarding quality control?**

A: Quality is priority. QC department with professional quality assurance specialist attaches great importance to quality control from the very beginning to the very end. Our factory has obtained Rohs, SGS, CE FCC, ISO9001:2008 authentication. Etc

**Q4: Factory? Yes! Can I customize the items I like, such as print our own logo or modify the design?**

A: Yes, we are a factory with more than 100 employees. We offer OEM/ODM service. Please contact us or our sales representative for details.

**Q5: Delivery time and warranty? What shipping service will you use for my products?**

A: Our lead time is around 2-4 weeks and we can offer 12 months warranty from delivery. We use DHL, Fedex, UPS, TNT, EMS as the customer.

**Q6: Where is your factory located? How can I visit there?**

A: Sure. We are more than happy to welcome you to Dongguan and show you around our workplace.