

## Product parameters

Product Name	Apple 8pin Lightning to Header Adapter with 10Pin Terminal Wire Harness
Connector	Lightninig Plug Male to Dupont 10pin terminal
Material	PVC+Copper
Cable Color	White or customized
Applied equipments	Laptop,Notebook,iPhone,iPad
Function	High speed data transfer,sync,PD fast charging
MOQ	100PCS

Apple lightning 8pin male to Dupont 2.54mm 10pin header cable for device's motherboard connecte,with PD fast charging and high speed data transfer cable and good for test and measurement on breadboards, Arduinos or computers.

In addition,we could provide other differernt connector with 5pin Dupont cable,such as [USB 2.0 A female to Dupont 5pin panel mount extension cable](#).

We can customize according to customer requirements for cable specifications, lengths, colors, and custom connector pinouts. Any questions, please feel free to contact us.

## Product Photo:









## **Company Info. Overview**



## About Us

10+ Years Experienced Professional Manufacturer of Customized Cables.



2000 M<sup>2</sup>  
Factory space with 10 years  
of production experience



100+  
Employees



OEM/ODM  
Support cable customized



TOP 500  
Bands approved  
manufacturer



## Certificate

We followed international ISO management Standard to make our custom cables, medical cables and chargers with good quality and best price.



# FAQ

## **Q1: Can I start a sample order before I order more?**

A: Sure, Heymed provide free sample if we have stock, customized sample need to be charged setup cost. We appreciate you asking us for a sample to check our quality.

## **Q2: What payment methods do you accept?**

A: PayPal, T/T, Bank Transfer, Western Union and L/C

## **Q3: How is your factory doing regarding quality control?**

A: Quality is priority. QC department with professional quality assurance specialist attaches great importance to quality control from the very beginning to the very end. Our factory has obtained Rohs, SGS, CE FCC, ISO9001:2008 authentication. Etc

## **Q4: Factory? Yes! Can I customize the items I like, such as print our own logo or modify the design?**

A: Yes, we are a factory with more than 100 employees. We offer OEM/ODM service. Please contact us or our sales representative for details.

## **Q5: Delivery time and warranty? What shipping service will you use for my products?**

A: Our lead time is around 2-4 weeks and we can offer 12 months warranty from delivery. We use DHL, Fedex, UPS, TNT, EMS as the customer.

## **Q6: Where is your factory located? How can I visit there?**

A: Sure. We are more than happy to welcome you to Dongguan and show you around our workplace. Our factory is located in 3rd. Floor, Building A, No.8 Kangyang 1st Street, Shebei Village, Huangjiang Town, Dongguan City, Guangdong, China.